


Q7145-1 Cut Sheet



Quabbin control and signal cable, unshielded, 8 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7145-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	8 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red, green, orange, blue, brown and yellow

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.232in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 666ft = 14 x 7in Reel, 667 to 728ft = 14 x 10in Reel, 729 to 1040ft = 16 x 10in Reel, 1041 to 1610ft = 18 x 10in Reel, 1611 to 2267ft = 18 x 13in Reel, 2268 to 2947ft = 24 x 17in Wooden Reel, 2948 to 6330ft = 30 x 17in Wooden Reel, 6331 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement