


Q7175-1 Cut Sheet



Quabbin control and signal cable, unshielded, 25 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7175-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	25 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red, green, orange, brown, blue, yellow, purple, gray, pink, tan, red/green, red/yellow, red/black, white/black, white/red, white/green, white/yellow, white/blue, white/brown, white/orange, white/gray, white/purple and white/black/red

Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.354in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 75ft = Coil• 76 to 310ft = 14 x 7in Reel• 311 to 445ft = 14 x 10in Reel• 446 to 680ft = 16 x 10in Reel• 681 to 955ft = 18 x 10in Reel• 956 to 1240ft = 18 x 13in Reel• 1241 to 2770ft = 24 x 17in Wooden Reel• 2771 to 4435ft = 30 x 17in Wooden Reel• 4436 to 5000ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830, E69976
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement