


Q7545-1 Cut Sheet



Quabbin control and signal cable, shielded, 8 conductors, 22 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q7545-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	8 conductors
Conductor Size	22 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Color Code 1

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.242in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 665ft = 14 x 7in Reel, 666 to 950ft = 14 x 10in Reel, 951 to 1460ft = 16 x 10in Reel, 1461 to 2040ft = 18 x 10in Reel, 2041 to 2650ft = 18 x 13in Reel, 2651 to 5930ft = 24 x 17in Wooden Reel, 5931 to 9485ft = 30 x 17in Wooden Reel, 9486 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830, E69976
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement