

Q8165-1 Cut Sheet



Quabbin control and signal cable, shielded, 3 conductors, 24 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q8165-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	3 conductors
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white and red

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.162in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 1367ft = 14 x 7in Reel, 1368 to 1494ft = 14 x 10in Reel, 1495 to 2134ft = 16 x 10in Reel, 2135 to 3302ft = 18 x 10in Reel, 3303 to 4650ft = 18 x 13in Reel, 4651 to 6045ft = 24 x 17in Wooden Reel, 6046 to 12983ft = 30 x 17in Wooden Reel, 12984 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement