

Q8170-1 Cut Sheet



Quabbin control and signal cable, shielded, 4 conductors, 24 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q8170-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	4 conductors
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC
Conductor Insulation Color	Black, white, red and green

Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.18in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 1107ft = 14 x 7in Reel, 1108 to 1210ft = 14 x 10in Reel, 1211 to 1728ft = 16 x 10in Reel, 1729 to 2675ft = 18 x 10in Reel, 2676 to 3766ft = 18 x 13in Reel, 3767 to 4896ft = 24 x 17in Wooden Reel, 4897 to 10516ft = 30 x 17in Wooden Reel, 10517 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement