


Q8185-1 Cut Sheet



Quabbin control and signal cable, shielded, 7 conductors, 24 AWG, 7-stranded, tinned copper, PVC conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q8185-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Wire/Cable Type	Control and signal
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2464
Application	General purpose
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	7 conductors
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	PVC

Conductor Insulation Color	Color Code 1
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.204in
Bulk Length	Cut to length
Package Type	1 to 99ft = Coil, 100 to 935ft = 14 x 7in Reel, 936 to 1340ft = 14 x 10in Reel, 1341 to 2055ft = 16 x 10in Reel, 2056 to 2870ft = 18 x 10in Reel, 2871 to 3730ft = 18 x 13in Reel, 3731 to 8345ft = 24 x 17in Wooden Reel, 8346 to MAX = 30 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E118830, E69976
CSA File #	LL51726
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement