


Q8606-1 Cut Sheet



Quabbin RS-422 low capacitance data serial cable, shielded, 3 twisted pairs, 24 AWG, 7-stranded, tinned copper, foam polypropylene conductor insulation material, PVC jacket, gray, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/Q8606-1>

Technical Specifications

Brand	Quabbin
Item	Cable
Protocol	Serial
Wire/Cable Type	RS-422 low capacitance data and serial
UL Wire/Cable Type	CM and AWM
Applicable Standards	UL 2448
Application	Data
Flexibility	Semi-flexible
Voltage Rating	300V
Conductors	3 twisted pairs
Conductor Size	24 AWG
Conductor Stranding	7-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Foam polypropylene

Conductor Insulation Color	Pair 1: black, red, pair 2: black, white and pair 3: black, green
Shielding	Shielded
Jacket Material	PVC
Jacket Color	Gray
Nominal Overall Cable Diameter	0.324in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 25 to 75ft = Coil• 76 to 370ft = 14 x 7in Reel• 371 to 530ft = 14 x 10in Reel• 531 to 815ft = 16 x 10in Reel• 816 to 1135ft = 18 x 10in Reel• 1136 to 1480ft = 18 x 13in Reel• 1481 to 3310ft = 24 x 17in Wooden Reel• 3311 to 5000ft = 30 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E118830
UL Recognized File #	E69976
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement