

QEU14-S Cut Sheet



NITRA pneumatic push-to-connect fitting, inline quick exhaust valve, technopolymer body, (1) 1/4in push-to-connect inlet(s), (1) 1/4in push-to-connect outlet(s), (1) silenced exhaust(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/QEU14-S>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Function	Inline quick exhaust valve
Body Material	Technopolymer
Fitting Measurement Type	SAE
Inlet Port	(1) 1/4in push-to-connect
Outlet Port	(1) 1/4in push-to-connect
Exhaust Port	(1) silenced
Operating Temperature	-4 to 140 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/QEU14-S.pdf>
See store item page for other formats.