

QMI7-0P-0A Cut Sheet



AutomationDirect photoelectric sensor, rectangular, diffuse, infrared light emission, 0-400mm sensing distance, selectable light-on/dark-on, PNP, potentiometer, 2 kHz switching frequency, plastic housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/QMI7-0P-0A>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Rectangular
Housing Size	21 x 12.8 x 31.2mm
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Diffuse
Operating Voltage	10-30 VDC
Number of Wires	3
Switching Output	PNP
Sensing Distance	0-400mm
Sensitivity	Potentiometer
Operation Mode	Selectable light-on/dark-on
Switching Frequency	2 kHz
Light emission	Infrared
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	24 AWG

Agency Approvals

UL Listed File #	E187310
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document