

# QMRS-0P-0F Cut Sheet



AutomationDirect photoelectric sensor, rectangular, background suppression, visible red, 30–200mm sensing distance, selectable light-on/dark-on, PNP, potentiometer, 21 x 12.8 x 31.2mm body, plastic, 4-pin M8 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/QMRS-0P-0F>

## Technical Specifications

<b>Brand</b>	AutomationDirect
<b>Item</b>	Photoelectric sensor
<b>Shape</b>	Rectangular
<b>IP Rating</b>	IP67
<b>Application</b>	Standard duty
<b>Housing Size</b>	21 x 12.8 x 31.2mm body
<b>Housing Material</b>	Plastic
<b>Sensing Method</b>	Background suppression
<b>Operating Voltage</b>	10–30 VDC
<b>Switching Output</b>	PNP

<b>Sensing Distance</b>	30–200mm
<b>Operation Mode</b>	Selectable light-on/dark-on
<b>Switching Frequency</b>	1 kHz
<b>Light Emission</b>	Visible red
<b>IO-Link Compatible</b>	No
<b>User Interface</b>	Potentiometer
<b>Connection</b>	4-pin M8 quick-disconnect
<b>Number of Wires</b>	3
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	E187310
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/QMRS-0P-0F.pdf>  
See store item page for other formats.