

QPSL-AP-42 Cut Sheet



ProSense digital pressure sensor, -14.5 to 14.5 psig range, Output: switch (N.O./N.C.), PNP selectable, Output 2: switch (N.O./N.C.), PNP selectable, Output 3: analog, 4-20 mA, 1/8in male NPT process connection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/QPSL-AP-42>

Technical Specifications

Brand	ProSense
Item	Digital pressure sensor
Pressure Range	-14.5 to 14.5 psig
Output	Switch (N.O./N.C.), PNP selectable
Output 2	Switch (N.O./N.C.), PNP selectable
Output 3	Analog, 4-20 mA
Display Type	Two-line, 4-digit, tri-color LCD display
Operating Voltage	11-26 VDC
Process Connection	1/8in male NPT
Electrical Connection	6.6ft/2m cable
Media Type	Gases

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/QPSL-AP-42.pdf>
See store item page for other formats.