

QTA-E181008CSWF Cut Sheet



Quadritalia OKK series enclosure kit, NEMA 12, 1800 x 1000 x 800mm (HxWxD), freestanding, carbon steel, RAL 7035 light gray, powder coat finish, single-door, acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/QTA-E181008CSWF>

Technical Specifications

Brand	Quadritalia
Item	Enclosure kit
Series	OKK
NEMA Rating	12
IP Rating	IP55
Nominal Enclosure Dimensions	1800 x 1000 x 800mm (HxWxD)
Enclosure Height	1807.00mm
Enclosure Width	1012.00mm
Enclosure Depth	812.00mm
Mounting	Freestanding
Dual Access	No
Material	Carbon steel
Color	RAL 7035 light gray
Finish	Powder coat
Cover Type	Single-door
Window Material	Acrylic
Kit Includes	(1) MTK180-4, (1) OKKTB1080, (1) PNA18A, (1) DTE18A, (1) RPE18A and (1) DLK188

Agency Approvals

UL Listed File #	None
UL Recognized File #	E503249
UL Hazardous File #	None
CE	View CE declarations
CSA File #	115232
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document