

R147-010-200R Cut Sheet



Hammond suspension arm fitting, straight wall-mount swing base, 170 degrees movement range, ductile iron, RAL 7040 window gray, powder coat finish. For use with 80mm Heavy Duty suspension arm profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R147-010-200R>

Technical Specifications

Brand	Hammond
Item	Suspension arm fitting
Fitting Type	Straight wall-mount swing base
Movement Range	170 degrees
Material	Ductile iron
Color	RAL 7040 window gray
Finish	Powder coat
For Use With	80mm Heavy Duty suspension arm profile

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/R147-010-200R.pdf>
See store item page for other formats.