

R149-005-001 Cut Sheet



Hammond suspension arm fitting, straight top-mount swivel base, 300 degrees movement range, aluminum, RAL 7040 window gray, powder coat finish. For use with 70mm taraPLUS suspension arm profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R149-005-001>

Technical Specifications

Brand	Hammond
Item	Suspension arm fitting
Fitting Type	Straight top-mount swivel base
Movement Range	300 degrees
Material	Aluminum
Color	RAL 7040 window gray
Finish	Powder coat
For Use With	70mm taraPLUS suspension arm profile

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/R149-005-001.pdf>
See store item page for other formats.