

R149-010-000 Cut Sheet



Hammond suspension arm fitting, straight wall-mount swivel base, 186 degrees movement range, aluminum, RAL 7040 window gray, powder coat finish. For use with 60 x 40mm taraPLUS suspension arm profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R149-010-000>

Technical Specifications

Brand	Hammond
Item	Suspension arm fitting
Fitting Type	Straight wall-mount swivel base
Movement Range	186 degrees
Material	Aluminum
Color	RAL 7040 window gray
Finish	Powder coat
For Use With	60 x 40mm taraPLUS suspension arm profile

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/R149-010-000.pdf>
See store item page for other formats.