

# R149-010-001 Cut Sheet



Hammond suspension arm fitting, right-angle wall-mount swivel base, 316 degrees movement range, aluminum, RAL 7040 window gray, powder coat finish. For use with 70mm taraPLUS suspension arm profile.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R149-010-001>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Suspension arm fitting
<b>Fitting Type</b>	Right-angle wall-mount swivel base
<b>Movement Range</b>	316 degrees
<b>Material</b>	Aluminum
<b>Color</b>	RAL 7040 window gray
<b>Finish</b>	Powder coat
<b>For Use With</b>	70mm taraPLUS suspension arm profile

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/R149-010-001.pdf>  
See store item page for other formats.