

R1838T-25 Cut Sheet



Minerallac side flange rod hanger, package of 25. For use with 1/8 to 1/4in side flange and 3/8-18 UNC threaded rod.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R1838T-25>

Technical Specifications

Brand	Minerallac
Item	Rod hanger
Hanger Type	Side flange
Load Rating	160 lbs
Material	Spring steel
Finish	Zinc phosphate plated
Minimum Flange Thickness	1/8in
Maximum Flange Thickness	1/4in
UL Type	UL 2239
Quantity per Pack	25
For Use With	1/8 to 1/4in side flange and 3/8-18 UNC threaded rod

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document