

R30-1-4AD Cut Sheet



Rockford Ball Screw R30 series ball screw, 0.631in, 0.2in/rev, 48in length, no end machining. For use with R302 and R302BS series ball nuts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R30-1-4AD>

Technical Specifications

Brand	Rockford Ball Screw
Item	Ball screw
Series	R30
Ball Screw Diameter	0.631in
Screw Lead	0.2in/rev
Length	48in
Dynamic Load Rating (C)	825lbf
Static Load Rating (CO)	6250lbf
End Machining	None
Thread Fabrication	Rolled
Pitch	0.2in
For Use With	R302 and R302BS series ball nuts

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/R30-1-4AD.pdf>
See store item page for other formats.