

R30-24347-1 Cut Sheet



Rockford Ball Screw R30 series ball screw, 0.631in, 0.2in/rev, 24in length, 2A one end machining. For use with R302 and R302BS series ball nuts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R30-24347-1>

Technical Specifications

| | |
|--------------------------------|----------------------------------|
| Brand | Rockford Ball Screw |
| Item | Ball screw |
| Series | R30 |
| Ball Screw Diameter | 0.631in |
| Screw Lead | 0.2in/rev |
| Length | 24in |
| Dynamic Load Rating (C) | 825lbf |
| Static Load Rating (CO) | 6250lbf |
| End Machining | 2A one end |
| Thread Fabrication | Rolled |
| Pitch | 0.2in |
| For Use With | R302 and R302BS series ball nuts |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/R30-24347-1.pdf>
See store item page for other formats.