

# R37-1-2AD Cut Sheet



Rockford Ball Screw R37 series ball screw, 0.75in, 0.5in/rev, 24in length, no end machining. For use with R372 and R372BS series ball nuts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R37-1-2AD>

## Technical Specifications

<b>Brand</b>	Rockford Ball Screw
<b>Item</b>	Ball screw
<b>Series</b>	R37
<b>Ball Screw Diameter</b>	0.75in
<b>Screw Lead</b>	0.5in/rev
<b>Length</b>	24in
<b>Dynamic Load Rating (C)</b>	3400lbf
<b>Static Load Rating (CO)</b>	21000lbf
<b>End Machining</b>	None
<b>Thread Fabrication</b>	Rolled
<b>Pitch</b>	0.25in
<b>For Use With</b>	R372 and R372BS series ball nuts

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/R37-1-2AD.pdf>  
See store item page for other formats.