

R37-24354-1 Cut Sheet



Rockford Ball Screw R37 series ball screw, 0.75in, 0.5in/rev, 24in length, 2A one end machining. For use with R372 and R372BS series ball nuts.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/R37-24354-1>

Technical Specifications

Brand	Rockford Ball Screw
Item	Ball screw
Series	R37
Ball Screw Diameter	0.75in
Screw Lead	0.5in/rev
Length	24in
Dynamic Load Rating (C)	3400lbf
Static Load Rating (CO)	21000lbf
End Machining	2A one end
Thread Fabrication	Rolled
Pitch	0.25in
For Use With	R372 and R372BS series ball nuts

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/R37-24354-1.pdf>
See store item page for other formats.