

RA14T-25 Cut Sheet



Minerallac right angle bracket rod hanger, package of 25. For use with 1/4in mounting hole and 1/4-20 UNC threaded rod.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RA14T-25>

Technical Specifications

Brand	Minerallac
Item	Rod hanger
Hanger Type	Right angle bracket
Load Rating	160 lbs
Material	Spring steel
Finish	Zinc phosphate plated
Mounting Holes	1/4in top
Quantity per Pack	25
For Use With	1/4in mounting hole and 1/4-20 UNC threaded rod

Agency Approvals

CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document