

RACPRO1-RD40 Cut Sheet



RECOM Power redundancy module, 2 inputs, 12/24/48 VDC nominal input, 12/24/48 VDC output, 40A, push terminals. Requires (2) matched 12, 24 or 48 VDC power supplies.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RACPRO1-RD40>

Technical Specifications

Brand	RECOM Power
Item	Redundancy module
Number of Inputs	2
Nominal Input Voltage	12/24/48 VDC
Input voltage range	9–56 VDC
Nominal Output Voltage	12/24/48 VDC
Output Voltage Range	12/24/48 VDC
Amperage Rating	40A

Protection Type(s)	overvoltage
Alarm Contact for Operation Monitoring	No
Active Current Sharing	No
Housing Material	Polycarbonate/aluminum
Mounting	35mm DIN rail
Connector Type	Push terminals
Requires	(2) matched 12, 24 or 48 VDC power supplies

Agency Approvals

UL Listed File #	None
UL Recognized File #	QQJQ2.E224736
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RACPRO1-RD40.pdf>
See store item page for other formats.