

RD1PD5CY Cut Sheet



Lumher RD machine vision lighting, ring light, white light emission, 5000K, plus or minus 30 degrees, continuous, 135 x 135 x 25mm housing, 22.8-25.2 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RD1PD5CY>

Technical Specifications

Brand	Lumher
Series	RD
Item	Machine vision lighting
Light Type	Ring light
Light Emission	White
Color Temperature	5000K
Beam Angle	Plus or minus 30 degrees
Housing Size	135 x 135 x 25mm
Inside Dimension	59mm diameter

Body Material	Anodized aluminum
Operation Mode	Continuous
Overdrive	No
Operating Voltage	22.8-25.2 VDC
Power Rating	7.6W
Current Consumption Continuous	0.32A
IP Rating	IP65
Connection	4-pin M12 quick-disconnect

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RD1PD5CY.pdf>
See store item page for other formats.