

# RD25.4SS Cut Sheet



Cembre knockout punch and die, ISO-25. For use with 7/16in draw stud. Punch and die included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RD25.4SS>

## Technical Specifications

<b>Brand</b>	Cembre
<b>Item</b>	Knockout punch and die
<b>Replacement</b>	No
<b>Knockout Size</b>	ISO-25
<b>Punch Shape</b>	Round
<b>Nominal Hole Size</b>	1.000in (25.4mm)
<b>Application</b>	Hole cutting
<b>For Use On</b>	Steel, plastic, stainless steel and non-ferrous metals
<b>For Use With</b>	7/16in draw stud
<b>Includes</b>	Punch and die
<b>Additional Information</b>	Draw stud not included

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>