

# RD2PF5CY Cut Sheet



Lumher RD machine vision lighting, ring light, infrared light emission, plus or minus 30 degrees, continuous, 225 x 225 x 25mm housing, 22.8-25.2 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RD2PF5CY>

## Technical Specifications

<b>Brand</b>	Lumher
<b>Series</b>	RD
<b>Item</b>	Machine vision lighting
<b>Light Type</b>	Ring light
<b>Light Emission</b>	Infrared
<b>Color Wavelength</b>	850 nm
<b>Beam Angle</b>	Plus or minus 30 degrees
<b>Housing Size</b>	225 x 225 x 25mm
<b>Inside Dimension</b>	135 x 135mm

<b>Body Material</b>	Anodized aluminum
<b>Operation Mode</b>	Continuous
<b>Overdrive</b>	No
<b>Operating Voltage</b>	22.8-25.2 VDC
<b>Power Rating</b>	8W
<b>Current Consumption Continuous</b>	0.33A
<b>IP Rating</b>	IP65
<b>Connection</b>	4-pin M12 quick-disconnect

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/RD2PF5CY.pdf>  
See store item page for other formats.