

RES90F16 Cut Sheet



Roxburgh EMI input filter, 120/240 VAC, 1-phase, 16A, panel mount, EMI/RFI filtering, multi-stage, drive rated, very high performance, 1/4in quick-disconnect. For use with 1-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RES90F16>

Technical Specifications

| | |
|---------------------------------|------------------------|
| Brand | Roxburgh |
| Item | Input filter |
| Filter Type | EMI |
| Filter Voltage Rating | 120/240 VAC |
| Number of Input Phases | 1 |
| Amperage Rating | 16A |
| On/Off Switch | No |
| Fused | No |
| Mounting | Panel |
| Filtering | EMI/RFI |
| Number of Filter Stages | Multi |
| SCCR Rating | 5kA SCCR |
| Filter Application | Drive rated |
| Filter Performance Level | Very high performance |
| Connector Type | 1/4in quick-disconnect |
| For Use With | 1-phase AC drives |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E191581 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |