


RF110B43CA Cut Sheet



AutomationDirect EMI input filter, 460 VAC, 3-phase, 25A, panel mount, EMI/RFI filtering, drive rated, standard performance, screw terminals and pigtail. For use with 3-phase AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RF110B43CA>

Technical Specifications

Brand	AutomationDirect
Item	Input filter
Filter Type	EMI
Filter Voltage Rating	460 VAC
Number of Input Phases	3
Amperage Rating	25A
On/Off Switch	No
Fused	No

Mounting	Panel
Filtering	EMI/RFI
SCCR Rating	5kA SCCR
Filter Application	Drive rated
Filter Performance Level	Standard performance
Connector Type	Screw terminals and pigtail
For Use With	3-phase AC drives

Agency Approvals

UL Listed File #	E79109
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document