

# RIA.2.233 Cut Sheet



SapiSelco releasable cable tie, 11.02in length, 0.3in width, 79.37lb tensile strength, 2.99in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RIA.2.233>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	Releasable
<b>Length</b>	11.02in
<b>Width</b>	0.3in
<b>Tensile Strength</b>	79.37lb
<b>Maximum Bundle Diameter</b>	2.99in
<b>Color</b>	Natural
<b>Material</b>	Nylon
<b>Temperature Rating</b>	+5 to +167 deg F
<b>Quantity per Pack</b>	100

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>