RIA.2.234 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

SapiSelco releasable cable tie, general purpose, nylon 6.6, 14.17in length, 0.3in width, 61 lb tensile strength, 3.94in maximum bundle diameter, natural. Package of 100.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/RIA.2.234

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Releasable
Performance	General purpose
Material	Nylon 6.6
Length	14.17in
Width	0.3in
Tensile Strength	61 lb

Maximum Bundle Diameter	3.94in
Color	Natural
UV Resistant	No
Temperature Rating	5–140 °F
Installation Temperature	+32 °F
Flammability	UL 94 V-2
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document