

RIQ-0242-H2 Cut Sheet



Roxburgh IEC inlet filter, 120/240 VAC, 1-phase, 2A, on/off switch, fused, snap-in mount, EMI/RFI filtering, 1-stage, general purpose, standard performance, 1/4in quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RIQ-0242-H2>

Technical Specifications

| | |
|---------------------------------|------------------------|
| Brand | Roxburgh |
| Item | Inlet filter |
| Filter Type | IEC |
| Filter Voltage Rating | 120/240 VAC |
| Number of Input Phases | 1 |
| Amperage Rating | 2A |
| On/Off Switch | Yes |
| Fused | Yes |
| Mounting | Snap-in |
| Filtering | EMI/RFI |
| Number of Filter Stages | 1 |
| SCCR Rating | 5kA SCCR |
| Filter Application | General purpose |
| Filter Performance Level | Standard performance |
| Connector Type | 1/4in quick-disconnect |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E191581 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 207414 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |