

# RJ1412HLL Cut Sheet



Stahlin RJ series enclosure, NEMA 1/3R/4X/6P/12, 14 x 12 x 7in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (2) twist-lock latches.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJ1412HLL>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Stahlin                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Series</b>                       | RJ                           |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>NEMA Rating</b>                  | 1/3R/4X/6P/12                |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 14 x 12 x 7in (HxWxD)        |
| <b>Enclosure Height</b>             | 15.50in                      |
| <b>Enclosure Width</b>              | 13.38in                      |
| <b>Enclosure Depth</b>              | 7.69in                       |
| <b>Mounting</b>                     | Wall                         |

|                                  |                                 |
|----------------------------------|---------------------------------|
| <b>Integral Mounting Feet</b>    | No                              |
| <b>Integral Mounting Flange</b>  | Yes                             |
| <b>Dual Access</b>               | No                              |
| <b>Knockouts</b>                 | No                              |
| <b>Material</b>                  | Fiberglass reinforced polyester |
| <b>Color</b>                     | Gray                            |
| <b>Cover Type</b>                | Raised single-door              |
| <b>Hinge Type</b>                | Continuous hinge                |
| <b>Number of Hinges Per Door</b> | 1                               |
| <b>Latch Type</b>                | (2) twist-lock latches          |
| <b>Padlockable</b>               | No                              |
| <b>Keylocking</b>                | No                              |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |