

RJ1816HLL Cut Sheet



Stahlin RJ series enclosure, NEMA 1/3R/4X/6P/12, 18 x 16 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (2) twist-lock latches.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJ1816HLL>

Technical Specifications

Brand	Stahlin	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	Yes
Series	RJ	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Fiberglass reinforced polyester
Vented	No	Color	Gray
NEMA Rating	1/3R/4X/6P/12	Cover Type	Raised single-door
IP Rating	IP66	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	18 x 16 x 10in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	19.63in	Latch Type	(2) twist-lock latches
Enclosure Width	17.48in	Shelf	No
Enclosure Depth	10.63in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RJ1816HLL.pdf>
See store item page for other formats.