

# RJ1816HPL Cut Sheet



Stahlin RJ series enclosure, NEMA 1/3R/4X/6P/12, 18 x 16 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (2) quick-release latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJ1816HPL>

## Technical Specifications

|                              |                              |
|------------------------------|------------------------------|
| Brand                        | Stahlin                      |
| Item                         | Enclosure                    |
| Series                       | RJ                           |
| Subpanel                     | Purchase subpanel separately |
| Slope Top                    | No                           |
| 3-Piece Assembly             | No                           |
| Vented                       | No                           |
| NEMA Rating                  | 1/3R/4X/6P/12                |
| IP Rating                    | IP66                         |
| Nominal Enclosure Dimensions | 18 x 16 x 10in (HxWxD)       |
| Enclosure Height             | 19.63in                      |
| Enclosure Width              | 17.48in                      |
| Enclosure Depth              | 10.63in                      |
| Mounting                     | Wall                         |
| Integral Mounting Feet       | No                           |

|                           |                                 |
|---------------------------|---------------------------------|
| Integral Mounting Flange  | Yes                             |
| Dual Access               | No                              |
| Knockouts                 | No                              |
| Bottom Gland Plate        | No                              |
| Material                  | Fiberglass reinforced polyester |
| Color                     | Gray                            |
| Cover Type                | Raised single-door              |
| Hinge Type                | Continuous hinge                |
| Number of Hinges Per Door | 1                               |
| Latch Type                | (2) quick-release latches       |
| Padlock Attachment Type   | Padlock hasp and staple         |
| Shelf                     | No                              |
| Padlockable               | Yes                             |
| Keylocking                | No                              |

## Agency Approvals

|                      |  |         |
|----------------------|--|---------|
| UL Listed File #     | E64358                                 | E362920 |
| UL Recognized File # | E333478                                |         |
| UL Hazardous File #  | None                                   |         |
| CE                   | <a href="#">View CE declarations</a>   |         |
| CSA File #           | LR069014                               |         |
| RoHS Status          | Yes (See CE Doc)                       |         |
| EU REACH             | <a href="#">View EU REACH document</a> |         |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/RJ1816HPL.pdf>  
See store item page for other formats.