

RJ606HLL Cut Sheet



Stahlin RJ series enclosure, NEMA 1/3R/4X/6P/12, 6 x 6 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (1) twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJ606HLL>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	RJ
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP66
Nominal Enclosure Dimensions	6 x 6 x 6in (HxWxD)
Enclosure Height	7.50in
Enclosure Width	7.53in
Enclosure Depth	6.32in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Raised single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(1) twist-lock latch
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64358	E362920
UL Recognized File #	E333478	
UL Hazardous File #	None	
CE	View CE declarations	
CSA File #	LR069014	
RoHS Status	Yes (See CE Doc)	
EU REACH	View EU REACH document	

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RJ606HLL.pdf>
See store item page for other formats.