

# RJ606HLL Cut Sheet



Stahlin RJ series enclosure, NEMA 1/3R/4X/6P/12, 6 x 6 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (1) twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJ606HLL>

## Technical Specifications

<b>Brand</b>	Stahlin
<b>Item</b>	Enclosure
<b>Series</b>	RJ
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>NEMA Rating</b>	1/3R/4X/6P/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	6 x 6 x 6in (HxWxD)
<b>Enclosure Height</b>	7.50in
<b>Enclosure Width</b>	7.53in
<b>Enclosure Depth</b>	6.32in
<b>Mounting</b>	Wall

<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	Yes
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	Fiberglass reinforced polyester
<b>Color</b>	Gray
<b>Cover Type</b>	Raised single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	(1) twist-lock latch
<b>Padlockable</b>	No
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E64358	E362920
<b>UL Recognized File #</b>	E333478	
<b>UL Hazardous File #</b>	None	
<b>CE</b>	<a href="#">View CE declarations</a>	
<b>CSA File #</b>	LR069014	
<b>RoHS Status</b>	Yes (See CE Doc)	
<b>EU REACH</b>	<a href="#">View EU REACH document</a>	