

# RJW1210HPL Cut Sheet



Stahlin RJW series enclosure, NEMA 1/3R/4X/6P/12, 12 x 10 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (2) quick-release latches, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJW1210HPL>

## Technical Specifications

<b>Brand</b>	Stahlin
<b>Item</b>	Enclosure
<b>Series</b>	RJW
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>NEMA Rating</b>	1/3R/4X/6P/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	12 x 10 x 6in (HxWxD)
<b>Enclosure Height</b>	13.56in
<b>Enclosure Width</b>	11.43in
<b>Enclosure Depth</b>	6.58in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	No

<b>Integral Mounting Flange</b>	Yes
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	Fiberglass reinforced polyester
<b>Color</b>	Gray
<b>Cover Type</b>	Raised single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	(2) quick-release latches
<b>Padlock Attachment Type</b>	Padlock hasp and staple
<b>Window Material</b>	SAR acrylic
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E64358
<b>UL Recognized File #</b>	E333478
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR069014
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>