

RJW1412HPL Cut Sheet



Stahlin RJW series enclosure, NEMA 1/3R/4X/6P/12, 14 x 12 x 7in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (2) quick-release latches, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJW1412HPL>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	RJW
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP66
Nominal Enclosure Dimensions	14 x 12 x 7in (HxWxD)
Enclosure Height	15.50in
Enclosure Width	13.38in
Enclosure Depth	7.69in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	Yes
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Raised single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(2) quick-release latches
Padlock Attachment Type	Padlock hasp and staple
Window Material	SAR acrylic
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64358	E362920
UL Recognized File #	E333478	
UL Hazardous File #	None	
CE	View CE declarations	
CSA File #	LR069014	
RoHS Status	Yes (See CE Doc)	
EU REACH	View EU REACH document	