

RJW1614HLL Cut Sheet



Stahlin RJW series enclosure, NEMA 1/3R/4X/6P/12, 16 x 14 x 7in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, (2) twist-lock latches, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJW1614HLL>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Stahlin |
| Item | Enclosure |
| Series | RJW |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/3R/4X/6P/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 16 x 14 x 7in (HxWxD) |
| Enclosure Height | 17.53in |
| Enclosure Width | 15.43in |
| Enclosure Depth | 7.68in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|----------------------------------|---------------------------------|
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | Gray |
| Cover Type | Raised single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | (2) twist-lock latches |
| Window Material | SAR acrylic |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |