

RJW1614HPL Cut Sheet



Stahlin RJW series enclosure, NEMA 1/3R/4X/6P/12, 16 x 14 x 7in (HxWxD), wall mount, fiberglass reinforced polyester, gray, raised single-door, quick-release latch, padlock hasp and staple, integral mounting flange, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RJW1614HPL>

Technical Specifications

Brand	Stahlin
Series	RJW
Item	Enclosure
Subpanel	Purchase subpanel separately
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP66
Nominal Enclosure Height	16in
Nominal Enclosure Width	14in
Nominal Enclosure Depth	7in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	Yes
Knockouts	No

Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Raised single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	Quick-release latch
Number Of Latches	2
Padlockable	Yes
Padlock Attachment Type	Padlock hasp and staple
Keylocking	No
Shelf	No
Window Material	SAR acrylic

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RJW1614HPL.pdf>
See store item page for other formats.