

RL9877-11 Cut Sheet



Dold phase monitor relay, 3-phase, 35mm DIN rail mount, 80-230 VAC input voltage, SPDT, 5A contact rating, screw terminal(s), LED indicator(s), phase reversal, phase unbalance, overvoltage, undervoltage, voltage range and neutral protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RL9877-11>

Technical Specifications

Brand	Dold	Connector Type	Screw terminal(s)
Item	Relay	Contact Rating	5A
Relay Type	Phase monitor	Indicator	LED
Number of Phases	3	Protection Type(s)	<ul style="list-style-type: none">• phase reversal• phase unbalance• overvoltage• undervoltage• voltage range• neutral
Mounting	35mm DIN rail		
Relay Housing Type	Finger-safe		
Input Voltage	80-230 VAC		
Relay Configuration	SPDT		

Agency Approvals

UL Listed File #	E107778
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/RL9877-11.pdf>
See store item page for other formats.