

RM25100-1CR-1 Cut Sheet



Bussmann modular fuse block, accepts R fuses, 100A, 250V, 1-pole, 14-1/0 AWG copper or aluminum, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM25100-1CR-1>

Technical Specifications

| | |
|----------------------------------|-------------------------------|
| Brand | Bussmann |
| Item | Fuse block |
| Modular | Yes |
| Blown Fuse Indicator | No |
| Multi-Wire | No |
| Accepts Fuse Class | R |
| Amperage Rating | 100A |
| Voltage Rating | 250V |
| Number of Poles | 1 |
| Conductor Size | 14-1/0 AWG copper or aluminum |
| Conductor Connection Type | Box lug |
| SCCR Rating | 200kA SCCR |
| Fuse Connection Type | Clip with reinforced spring |
| Mounting | Panel |
| Additional Information | Covers sold separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E14853 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 47235 - 6225-01 |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |