

# RM60100-1CR-2 Cut Sheet



Bussmann modular fuse block, accepts R fuses, 100A, 600V, 2-pole, 14-1/0 AWG copper or aluminum, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM60100-1CR-2>

## Technical Specifications

|                      |            |
|----------------------|------------|
| Brand                | Bussmann   |
| Item                 | Fuse block |
| Modular              | Yes        |
| Blown Fuse Indicator | No         |
| Multi-Wire           | No         |
| Accepts Fuse Class   | R          |
| Amperage Rating      | 100A       |
| Voltage Rating       | 600V       |

|                           |                               |
|---------------------------|-------------------------------|
| Number of Poles           | 2                             |
| Conductor Size            | 14-1/0 AWG copper or aluminum |
| Conductor Connection Type | Box lug                       |
| SCCR Rating               | 200kA SCCR                    |
| Fuse Connection Type      | Clip with reinforced spring   |
| Mounting                  | Panel                         |
| Additional Information    | Covers sold separately        |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | E14853                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | <a href="#">View CE declarations</a>   |
| CSA File #           | 47235 - 6225-01                        |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |
| Other                | None                                   |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/RM60100-1CR-2.pdf>  
See store item page for other formats.