

RSC182408G Cut Sheet



Wiegmann enclosure, NEMA 1/3R, 24 x 18 x 8in (HxWxD), wall mount, galvanized steel, screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSC182408G>

Technical Specifications

| | |
|---------------------------------|-----------|
| Brand | Wiegmann |
| Item | Enclosure |
| Slope Top | No |
| NEMA Rating | 1/3R |
| Nominal Enclosure Height | 24in |
| Nominal Enclosure Width | 18in |
| Nominal Enclosure Depth | 8in |
| Mounting | Wall |
| Integral Mounting Feet | No |

| | |
|---------------------------------|-------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | Galvanized steel |
| Cover Type | Screw cover |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E23553 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RSC182408G.pdf>
See store item page for other formats.