

RSC202408G Cut Sheet



Wiegmann enclosure, NEMA 1/3R, 24 x 20 x 8in (HxWxD), wall mount, galvanized steel, screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSC202408G>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Slope Top	No
NEMA Rating	1/3R
Nominal Enclosure Height	24in
Nominal Enclosure Width	20in
Nominal Enclosure Depth	8in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Galvanized steel
Cover Type	Screw cover
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RSC202408G.pdf>
See store item page for other formats.