

RSC243612 Cut Sheet



Wiegmann enclosure, NEMA 1/3R, 36 x 24 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSC243612>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Slope Top	No
NEMA Rating	1/3R
Nominal Enclosure Height	36in
Nominal Enclosure Width	24in
Nominal Enclosure Depth	12in
Mounting	Wall
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E23553
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/RSC243612.pdf>
See store item page for other formats.