

RSCG040436 Cut Sheet



Wiegmann wiring trough, 4 x 4 x 36in (HxDxL), NEMA 1/3R, wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSCG040436>

Technical Specifications

Brand	Wiegmann
Item	Wiring trough
NEMA Rating	1/3R
Nominal Enclosure Dimensions	4 x 36 x 4in (HxWxD)
Enclosure Height	4.06in
Enclosure Depth	4.06in
Enclosure Length	36.00in
Mounting	Wall
Knockouts	Yes
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover

Agency Approvals

UL Listed File #	E32576
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document