

RSCG060612 Cut Sheet



Wiegmann wiring trough, 6 x 6 x 12in (HxDxL), NEMA 1/3R, wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSCG060612>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Wiegmann |
| Item | Wiring trough |
| NEMA Rating | 1/3R |
| Nominal Enclosure Dimensions | 6 x 12 x 6in (HxWxD) |
| Enclosure Height | 6.06in |
| Enclosure Depth | 6.06in |
| Enclosure Length | 12.00in |
| Mounting | Wall |
| Knockouts | Yes |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Screw cover |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E32576 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |