

# RSCG060612 Cut Sheet



Wiegmann wiring trough, 6 x 6 x 12in (HxDxL), NEMA 1/3R, wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSCG060612>

## Technical Specifications

Brand	Wiegmann
Item	Wiring trough
NEMA Rating	1/3R
Nominal Enclosure Dimensions	6 x 12 x 6in (HxWxD)
Enclosure Height	6.06in
Enclosure Depth	6.06in
Enclosure Length	12.00in
Mounting	Wall
Knockouts	Yes
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Screw cover

## Agency Approvals

UL Listed File #	E32576
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>