

# RSCG060648 Cut Sheet



Wiegmann wiring trough, 6 x 6 x 48in (HxDxL), NEMA 1/3R, wall mount, with knockouts, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RSCG060648>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Wiring trough
<b>NEMA Rating</b>	1/3R
<b>Nominal Enclosure Dimensions</b>	6 x 48 x 6in (HxWxD)
<b>Enclosure Height</b>	6.06in
<b>Enclosure Depth</b>	6.06in
<b>Enclosure Length</b>	48.00in
<b>Mounting</b>	Wall
<b>Knockouts</b>	Yes
<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	Screw cover

## Agency Approvals

<b>UL Listed File #</b>	E32576
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>